



Hello [First Name]

This is a friendly reminder that our webinar, "Next Generation Microswitches: Integrating Resistors for Smart Fault Detection" with Roland Hiso is happening tomorrow!

Event Details:

- **Title:** Next Generation Microswitches: Integrating Resistors for Smart Fault Detection
- **Date:** Tuesday, March 24, 2026
- **Time:** 11:00 a.m. CT/ 12:00 p.m. ET

In this webinar, OMRON will present how integrated resistors can transform microswitches into smart sensors, including key highlights:


- Overview of D2AW-R and D2EW-R families.
- Economic benefits: reduced components, assembly time, and downtime.
- Guidance on implementing four-state detection.

We're excited to have Roland Hiso as our featured speaker, and we're confident that you'll find the session both informative and engaging.

There is still time to secure your spot and join the webinar. Register today!

[REGISTER HERE](#)

OMRON Membership Program



For a limited time, we will be offering our membership program free to anyone who signs up for it.

- Free download of 2D/3D CAD and ECAD files
- Updated information on New Products
- Access to Omron's exclusive newsletter
- Downloadable RoHS Certifications
- Reference History
- And more to come...

[Sign Up For Membership](#)

[Visit Our Website](#) | [Contact Us](#)

[Relays](#) | [Switches](#) | [Connectors](#) | [Sensors](#)

